

# **Grande Fleur-eo**



Refrigerated Heating Circulator with air-cooled refrigerating unit. Powerful, variable speed pump, housing of stainless steel, CFC and H-CFC free. Speed controlled pump (soft start), pump pressure control. With adjustable overtemperature protection according to DIN 12876.

## Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

### further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

3-2-2 warranty - registration required.

#### Please note

The machine is developed exclusively for external open operation, and does not possess an expansion tank. The filling of the thermofluid, and allowance for the temperature dependent volume changes is only possible via an externally connected application.

# Technical data according to DIN 12876

Operating temperature range Temperature stability at -10°C temperature set point / display Resolution of display Internal temperature sensor Sensor external connection

digital input digital output Alarm message Safety classification Heating power

Interface digital

Cooling power with at 200°C at 150°C at 100°C at 50°C

at 20°C Cooling power with

at 0°C at -20°C at -30°C at -40°C

Refrigeration machine

Refrigerant
Gas warning sensor
Circulation pump:

max. delivery pressure Pump connection

max. permissible kin. viscosity min. filling capacity

-40...200 °C 0.01 K

5,7" colour Touchscreen

0,01 K Pt100 Pt100

Ethernet, USB (Host u. Device), RS232

ECS ONE POKO ONE

optic, acoustic, relay

optic, acoustic Class III / FL 1,5 kW Thermooil 0,6 kW 0,6 kW 0,6 kW 0,6 kW 0,6 kW Ethanol 0,6 kW

0,35 kW 0,2 kW 0,04 kW

air-cooled, natural refrigerant

R290 without

47 l/min 0.9 bar M24x1,5 male 50 mm²/s 1.5 l



Order-No.: 1041.0004.01

## Technical data according to DIN 12876

Overall dimensions WxDxH \*\*

Net weight

Power supply requirement

Degree of Protection

min. ambient temperature

max. ambient temperature

295x540x565 mm

55 kg

230V 1~ 50Hz

IP20

min. 200

Example 100

Example 200

Exampl

from Serial-No.: 1.0/17

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: mini-USB cable #54949\*, E-grade "Professional" #9496\*, E-grade "Explore" #10495, Adaptor M16x1 male to M24x1,5 female\*, SpyLight-Software, Com.G@te, Thermofluid, metal hoses M16x1 or M24x1,5, external pressure sensor

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

Output data valid for: Room temperature 20°C

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

<sup>\*</sup> standard equipment

<sup>\*\*</sup> Please respect space requirements. See operating conditions at www.huber-online.com