

Chiller with water-cooled refrigerating unit and circulation pump. Evaporator (cooler), tank and housing of stainless steel. Pump made of industrial plastic material. Digital Temperature adjustment and digital temperature display. Adjustable bypass. Level indicator with sight glass. With adjustable overtemperature protection according to DIN 12876.

Unichiller „P“ Models: Circulating pumps with a high discharge pressure for applications with high pressure drops.

#### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

#### Technical data according to DIN 12876

Operating temperature range	-20...100 °C	
temperature set point / display	5,7" colour Touchscreen	
Internal temperature sensor	Pt100	<b>Order-No.: 3012.0218.01</b>
Sensor external connection	Pt100	
Temperature stability at -10°C	0,5 K	
Interface digital	Ethernet, USB (Host u. Device), RS232	
Safety classification	Class III / FL	
Heating power	2 kW	
Cooling power		
at 15°C	0,7 kW	
at 0°C	0,55 kW	
at -10°C	0,4 kW	
at -20°C	0,2 kW	
Refrigeration machine	water-cooled, CFC- and HCFC-free	
Refrigerant	R507	
Refrigerant quantity	0,36 kg	
Circulation pump	B	
max. delivery	25 l/min	
max. delivery pressure	2,5 bar	
Delivery at 0,5 bar	21 l/min	
Delivery at 1,0 bar	17 l/min	
Delivery at 1,5 bar	11 l/min	
Delivery at 2,0 bar	6 l/min	
Pump connection	G3/4 male	
Cooling water connection	G1/2 male	
min. cooling water differential pressure	3 bar	
max. cooling water pressure	6 bar	
min. filling capacity	3,8 l	
Volume of expansion	1,7 l	
Overall dimensions WxDxH **	350x496x622 mm	
Power supply requirement	230V 1~ 50/60Hz	

## Technical data according to DIN 12876

---

Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

---

from Serial-No.:

1.0/17

---

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: mini-USB cable #54949\*, Hose coupling for G3/4 male\*, hose coupling cooling water for G1/2 male\*, cover expansion tank\*, connection tubes, braided hoses for cooling water, Com.G@te.

\* standard equipment

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 3 bar differential pressure between cooling water inlet and - outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materials used in the cooling water circuit include: copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer). It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)