

Heating Circulator for closed systems and open baths. Powerful - regulated - cooling, saves water, unpressurised. Stepper motor controlled HT cooler (High temperature cooler) and air-cooled heat exchanger. Closed circulation pump made of stainless steel with cooled shaft seal with free shaft, without bearing in the liquid. Automatical capacity adaption for heating. Expansion tank (not thermoregulated) for closed systems, lockable for open baths. Heat exchanger, moistened parts and housing made of stainless steel. With adjustable overtemperature protection according to DIN 12876.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range	65... 300 °C
Temperature stability at 70°C	0,01 K
temperature set point / display	5,7" colour Touchscreen
Resolution of display	0,01 K
Internal temperature sensor	Pt100
External sensor	Pt100
Interface digital	Ethernet, USB (Host u. Device), RS232
digital input	ECS ONE
digital output	POKO ONE
Alarm message	optic, acoustic, relay
Safety classification	Class III / FL
Heating power convertible	3,0kW or 6,0kW
Cooling power at 300°C	3,2 kW
Cooling power at 200°C	2,3 kW
Cooling power at 100°C	0,6 kW
Circulation pump:	
max. delivery	45 l/min
max. delivery pressure	0.9 bar
Pump connection	M24x1,5 male
max. permissible kin. viscosity	50 mm ² /s
min. filling capacity	1,9 l
Filling capacity expansion tank	2,8 l
Overall dimensions WxDxH **	425x250x631 mm
Net weight	41 kg
sound pressure level +/- 4 dB(A)	54 dB(A)
Power supply convertible	230V 1~ 50/60Hz* or 400V 3~N 50/60Hz
max. current	14,5 A
max. current (3 Phase)	10 A
Fuse (1 phase)	16 A
Fuse (3 phase)	3x10 A
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C



Order-No.: 1003.0020.01

from Serial-No.: 218993

1.0/15

Technical data according to DIN 12876

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: E-grade "Professional" #9496*, mini-USB cable *, E-grade "Explore" #10495, Com.G@te Namur, PC-Com.G@te-cabel, Holder for Com.G@te #10019, Com.G@te-extension cable: upon request, SpyLight-Software, Thermofluid, external pressure sensor, metal hoses, external sensor, connecting cable, float switch in sight glass for extended security.

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

* standard equipment

Output data valid for: Room temperature 20° C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and + 3% frequency -> not allowed !

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Alternative (factory set) power supply - please quote configuration at time of ordering.

** Please respect space requirements. See operating conditions at www.huber-online.com