Unistat TR401w HT

High Temperature Thermostat using the unistat principal with Plug & Play technology. Minimized volume, shortest possible heating times, hydraulically closed: No oil vapour. The cooling water discharge temperature is limited to 55 °C to prevent steam from being generated during cooling at flow temperatures in excess of 100 °C. Housing and heat exchanger made of stainless steel. With adjustable overtemperature protection according to DIN 12876. Length of cable between machine and controller approx. 5m.

Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range

min. operating temperature range w. water cooling

Temperature stability at 70°C temperature set point / display

Absolute accuracy

Internal temperature sensor

External sensor Interface digital

digital input digital output Alarm message Safety classification Heating power convertible Cooling power at 100°C Cooling power at 200°C Cooling power at 300°C Cooling power at 400°C Circulation pump:

max. delivery max. delivery pressure Delivery at 0,2 bar Delivery at 0,4 bar Delivery at 0,6 bar Pump connenction flow Pump connection return Cooling water connection

Cooling water consumption at water temp.15°C

min. filling capacity Volume of expansion

min. cooling water differential pressure

max. cooling water pressure Overall dimensions WxDxH

Net weight

Power supply convertible

max. current

50...400 °C 15 °C 0.05 K

5,7" colour Touchscreen 2-point-calibration

Pt100 Pt100

Ethernet, USB (Host u. Device), RS232 **ECS ONE POKO ONE**

optic, acoustic, relay Class III / FL

3,0kW or 9,0kW

10 kW 10 kW 10 kW 10 kW

26 l/min 0.8 bar 23 I/min 18 l/min 12 I/min M24x1,5

M24x1,5 G1/2 male 240 l/h 2,3 | 5 I 3 bar

288x379x890 mm

54 ka

6 bar

230V 1~ 50/60Hz* or 400V 3~N 50/60Hz

14,5 A



Order-No.: 1028.0018.01

Technical data according to DIN 12876

205790	1.0/15
40 °C	
5 °C	
3x16 A	
14,5 A	
16 A	
	14,5 A 3x16 A 5 °C 40 °C

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: E-grade "Professional" #9496*, mini-USB cable #54949*, Cover level indicator*, connection cable (order no.: 13482)*, E-grade "Explore" #10495, expansion tank upgrades may be retrofitted for any volume required, connection tubes, braided hoses for cooling water, external sensor, retort stand holder, Com.G@te, Holder for Com.G@te #10019; Com.G@te-extension cable # 16160

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 3 bar differential pressure between cooling water inlet and outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materiels used in the cooling water circuit include; copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and +3% frequency -> not allowed!

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Alternative (factory set) power supply - please quote configuration at time of ordering.

** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

^{*} Standard equipment