

Unistat TR402

High Temperature Thermostat using the unistat principal with Plug & Play technology. Minimized volume, shortest possible heating times, hydraulically closed: No oil vapour. Housing and heat exchanger made of stainless steel. Length of cable between machine and controller approx. 5m.

Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

3-2-2 warranty - registration required.

- Expansion tank lid can be fixed in place. The lid has connections for a nitrogen blanket (maximum pressure 0,2 bar)
- Additional heaters with over-temperature protection for expansion vessel and internal pipework

Technical data according to DIN 12876

Operating temperature range Temperature stability at 70°C temperature set point / display Absolute accuracy Internal temperature sensor

External sensor

External sensor Interface digital

digital input digital output Alarm message Safety classification Heating power convertible

Circulation pump: max. delivery max. delivery pres

max. delivery pressure
Pump connection flow
Pump connection return
Cooling water connection
min. filling capacity
Volume of expansion
Overall dimensions WxDxH

Net weight

Power supply convertible

max. current
Fuse (1 phase)
max. current (3 Phase)
Fuse (3 phase)
min. ambient temperature
max. ambient temperature

80...425 °C 0.05 K

5,7" colour Touchscreen 2-point-calibration

Pt100 Pt100

Ethernet, USB (Host u. Device), RS232 ECS ONE POKO ONE

optic, acoustic, relay Class III / FL 3,0kW or 9,0kW

31 l/min 1 bar M24x1,5 M24x1,5 G1/2 male

3 I 2,9 I

288x332x870 mm

48 kg

230V 1~ 50/60Hz* or 400V 3~N 50/60Hz

16 A 16 A 16 A 3x16 A 5 °C 40 °C



Order-No.: 1028.0006.01

from Serial-No.:

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: E-grade "Professional" #9496*, mini-USB cable #54949*, Cover level indicator*, connection cable (order no.: 13482)*, E-grade "Explore" #10495, expansion tank upgrades may be retrofitted for any volume required, connection tubes, braided hoses for cooling water, external sensor, retort stand holder, Com.G@te, Holder for Com.G@te #10019; Com.G@te-extension cable # 16160

* Standard equipment

Output data valid for: Room temperature 20°C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and + 3% frequency -> not allowed!

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Alternative (factory set) power supply - please quote configuration at time of ordering.

** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com